



PowderTAG	V.S	Powder Checker
Ultraviolet light source technology	Technology	Ultrasonic technology
64 - 1024 ms	Measuring speed	1 - 3 sec or in SCAN MODE continuously
± 3%	Measuring accuracy	±5 micron
50 - 300 microns	Measuring range	20 -100 micron
Any angle (no need for perpendicular aim)	Probe handling	perpendicular
about 35 mm	Measuring distance	about 19 mm
3 LED pointers for guiding	Measuring spot location	-
Ø 1mm	Measuring spot size	2mm
10 hours of continuous use	Battery capacity	4 AAA batteries
YES	For Uncured Powder (before the oven)	YES
YES	For Cured Powder (after the oven)	NO
All powders	Powder type range	All powders